



- SPECIFICATIONS**
- 1、Current Rating: 3A AC, DC
  - 2、Voltage Rating: 250V AC, DC
  - 3、Temperatuer Range:  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
  - 4、Contact Resistance:  $20\text{m}\Omega$  Max
  - 5、Insulation Resistance:  $1000\text{m}\Omega$  Min
  - 6、Withstanding Voltang: 800V AC/minute
  - 7、Material: Housing Nylon66 UL94-V0(2)

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	FG-PHD-2x2Y	2.00	6.00	4.40
3	FG-PHD-2x3Y	4.00	8.00	6.40
4	FG-PHD-2x4Y	6.00	10.00	8.40
5	FG-PHD-2x5Y	8.00	12.00	10.40
6	FG-PHD-2x6Y	10.00	14.00	12.40
7	FG-PHD-2x7Y	12.00	16.00	14.40
8	FG-PHD-2x8Y	14.00	18.00	16.40
9	FG-PHD-2x9Y	16.00	20.00	18.40
10	FG-PHD-2x10Y	18.00	22.00	20.40
11	FG-PHD-2x11Y	20.00	24.00	22.40
12	FG-PHD-2x12Y	22.00	26.00	24.40
13	FG-PHD-2x13Y	24.00	28.00	26.40
14	FG-PHD-2x14Y	26.00	30.00	28.40
15	FG-PHD-2x15Y	28.00	32.00	30.40
16	FG-PHD-2x16Y	30.00	34.00	32.40
17	FG-PHD-2x17Y	32.00	36.00	34.40
18	FG-PHD-2x18Y	34.00	38.00	36.40
19	FG-PHD-2x19Y	36.00	40.00	38.40
20	FG-PHD-2x20Y	38.00	42.00	40.40

		GENERAL TOLERANCE		制图 DRAWING		深圳市富港科技有限公司			
		DIM TOL		审核 CHECK					
		X.X $\pm 0.30$		批准 APPROVAL		产品名称 TITLE	PHD (2.00) 双排孔座	版本 REV.	A
1		初版发行		X.XX $\pm 0.20$		产品料号 PART NO.	FG-PHD-2xNY	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle $\pm 3.0^{\circ}$	投影 Projection		材料 MATERIAL		页次 SHEET	1/1