



技术指标:

1. 温度范围: -25°C~85°C.
2. 额定电压: 250V AC,DC.
3. 耐电压: 1500V AC/minute.
4. 接触电阻: ≤20mΩ .
5. 绝缘电阻: ≥1000MΩ.
6. 额定电流: 5A AC,DC.

材料:

1. 塑胶: PA66 黑色

型号	CKT	A	B
ZX-5557-4.2-2-1P-HGJK	2*1	0.00	5.50
ZX-5557-4.2-2-2P-HGJK	2*2	4.20	9.70
ZX-5557-4.2-2-3P-HGJK	2*3	8.40	13.90
ZX-5557-4.2-2-4P-HGJK	2*4	12.60	18.10
ZX-5557-4.2-2-5P-HGJK	2*5	16.80	22.30
ZX-5557-4.2-2-6P-HGJK	2*6	21.00	26.50
ZX-5557-4.2-2-7P-HGJK	2*7	25.20	30.70
ZX-5557-4.2-2-8P-HGJK	2*8	29.40	34.90
ZX-5557-4.2-2-9P-HGJK	2*9	33.40	39.10
ZX-5557-4.2-2-10P-HGJK	2*10	37.80	43.30
ZX-5557-4.2-2-11P-HGJK	2*11	42.00	47.50
ZX-5557-4.2-2-12P-HGJK	2*12	46.20	51.70

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE	料号 PART NO.	ZX-5557-4.2-2-NP-HGJK	版本 REV.	A
			.X±0.30	X.*±5°	审核 CHECK	LEO	品名 TITLE	WBM4.2MM HOUSING	页次 SHEET	1/1
			.XX±0.25	X.X*±1°	核准 APPROVAL	JOHN	客户料号 CUTM.NO.			
			.XXX±0.15		单位 UNITS	MM	比例 SCALE	1:1	兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.	