



Part No	Pin	A	B	C	D	E
ZX-HY2.0-2PJK	2	2.00	4.70	2.30	1.00	0.60
ZX-HY2.0-3PJK	3	4.00	6.70	2.30	1.00	0.60
ZX-HY2.0-4PJK	4	6.00	8.70	4.30	1.70	1.00
ZX-HY2.0-5PJK	5	8.00	10.70	4.30	1.70	1.00
ZX-HY2.0-6PJK	6	10.00	12.70	8.30	5.90	1.95
ZX-HY2.0-7PJK	7	12.00	14.70	10.30	7.90	1.95
ZX-HY2.0-8PJK	8	14.00	16.70	12.30	9.90	1.95
ZX-HY2.0-9PJK	9	16.00	18.70	12.30	9.90	1.95
ZX-HY2.0-10PJK	10	18.00	20.70	12.30	9.90	1.95
ZX-HY2.0-11PJK	11	20.00	22.70	16.30	13.90	1.95
ZX-HY2.0-12PJK	12	22.00	24.70	16.30	13.90	1.95
ZX-HY2.0-13PJK	13	24.00	26.70	16.30	13.90	1.95
ZX-HY2.0-14PJK	14	26.00	28.70	16.30	13.90	1.95
ZX-HY2.0-15PJK	15	28.00	30.70	16.30	13.90	1.95
ZX-HY2.0-16PJK	16	30.00	32.70	16.30	13.90	1.95



技术要求 Specification:

1. 材质 Material: PA66 UL94V-0;
2. 额定电流 Current rating: 2.0A AC, DC
3. 额定电压 Voltage rating: 250V AC, DC
4. 温度范围 Temperature range: -25°C to +85°C
5. 接触电阻 Contact resistance: ≤ 20mΩ
6. 绝缘电阻 Insulation resistance: ≥ 1000MΩ
7. 耐压 Withstand voltage: 500V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

此凸点只限 10PIN 以上的产品有,  
2-10PIN 均无此凸点

Plastic surface smooth and clean, no obvious glitches, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING
			.X±0.30	X.*±1*	ROSE
			.XX±0.20		LEO
			.XXX±0.10		JOHN
					单位 UNITS

ROSE	料号 PART NO.	ZX-HY2.0-NPJK	版本 REV.	A
LEO	品名 TITLE	HY2.0MM HOUSING	页次 SHEET	1/1
JOHN	客户料号 CUTM.NO.			
MM	比例 SCALE	1:1		



兆星精密电子(深圳)有限公司  
ShenZhen ZhaoXing Precision electronics Co., Ltd.