



技术指标:

1. 温度范围:  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ .
2. 额定电压: 250V AC,DC.
3. 耐电压: 800V AC/minute.
4. 接触电阻:  $\leq 20\text{m}\Omega$ .
5. 绝缘电阻:  $\geq 1000\text{M}\Omega$ .
6. 额定电流: 3A AC,DC.

型号	CKT	A	B	C
ZX-PHB2.0-2-2PJK	2*2	2.00	7.00	2.90
ZX-PHB2.0-2-3PJK	2*3	4.00	9.00	3.10
ZX-PHB2.0-2-4PJK	2*4	6.00	11.00	4.30
ZX-PHB2.0-2-5PJK	2*5	8.00	13.00	6.30
ZX-PHB2.0-2-6PJK	2*6	10.00	15.00	8.30
ZX-PHB2.0-2-7PJK	2*7	12.00	17.00	6.30
ZX-PHB2.0-2-8PJK	2*8	14.00	19.00	8.30
ZX-PHB2.0-2-9PJK	2*9	16.00	21.00	14.30
ZX-PHB2.0-2-10PJK	2*10	18.00	23.00	14.30
ZX-PHB2.0-2-11PJK	2*11	20.00	25.00	14.30
ZX-PHB2.0-2-12PJK	2*12	22.00	27.00	14.30
ZX-PHB2.0-2-13PJK	2*13	24.00	29.00	14.30
ZX-PHB2.0-2-14PJK	2*14	26.00	31.00	14.30
ZX-PHB2.0-2-15PJK	2*15	28.00	33.00	14.30
ZX-PHB2.0-2-16PJK	2*16	30.00	35.00	14.30
ZX-PHB2.0-2-22PJK	2*22	42.00	47.00	14.30

序号	品名	材质		
1	胶壳	PA66		

  

制图	品名	料号	版本	页次
DRAWING	ROSE	PART NO. ZX-PHB2.0-2-NPJK	REV. A	1/1
CHECK	LEO	TITLE PHB2.0公头胶壳	SHEET	
APPROVAL	JOHN	CUTM.NO.		
UNIT	MM	SCALE 1:1		

  

兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.	
---	--

制图	变更内容	日期	GENERAL TOLERANCE	
DRAWN	DESCRIPTION	DATE	X.±0.30	X.±5°
			.X±0.25	.X±1°
			.XX±0.15	