



NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating: 125V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

| Part No | Pin | A | B | C | D |
|-----------------|-----|-------|-------|-------|-------|
| ZX-MX1.25-2PWZ | 2 | 1.25 | 4.40 | 3.20 | / |
| ZX-MX1.25-3PWZ | 3 | 2.50 | 5.65 | 4.45 | / |
| ZX-MX1.25-4PWZ | 4 | 3.75 | 6.90 | 5.70 | 2.50 |
| ZX-MX1.25-5PWZ | 5 | 5.00 | 8.15 | 6.95 | 3.75 |
| ZX-MX1.25-6PWZ | 6 | 6.25 | 9.40 | 8.20 | 5.00 |
| ZX-MX1.25-7PWZ | 7 | 7.50 | 10.65 | 9.45 | 6.25 |
| ZX-MX1.25-8PWZ | 8 | 8.75 | 11.90 | 10.70 | 7.50 |
| ZX-MX1.25-9PWZ | 9 | 10.00 | 13.15 | 11.95 | 8.75 |
| ZX-MX1.25-10PWZ | 10 | 11.25 | 14.40 | 13.20 | 10.00 |
| ZX-MX1.25-11PWZ | 11 | 12.50 | 15.65 | 14.45 | 11.25 |
| ZX-MX1.25-12PWZ | 12 | 13.75 | 16.90 | 15.70 | 12.50 |
| ZX-MX1.25-13PWZ | 13 | 15.00 | 18.15 | 16.95 | 13.75 |
| ZX-MX1.25-14PWZ | 14 | 16.25 | 19.40 | 18.20 | 15.00 |
| ZX-MX1.25-15PWZ | 15 | 17.50 | 20.65 | 19.45 | 16.25 |
| ZX-MX1.25-16PWZ | 16 | 18.75 | 21.90 | 20.70 | 17.50 |

| 制图 DRAWN | 变更内容 DESCRIPTION | 日期 DATE | GENERAL TOLERANCE | | 制图 DRAWING |
|-------------|---------------------|------------|-------------------|-----------|---------------|
| | | | .X±0.20 | X'':±5° | ROSE |
| | | | .XX±0.10 | X.X':±3° | LEO |
| | | | .XXX±0.05 | X.XX':±1° | JOHN |
| | | | | | 单位 UNITS |

| | | | |
|---|----------------|-------------|-----|
| 料号 PART NO. | ZX-MX1.25-NPWZ | 版本 REV. | A |
| 品名 TITLE | WAFER 1.25 弯针 | 页次 SHEET | 1/1 |
| 客户料号 CUTM.NO. | | | |
| 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd. | | | |

MM 比例 SCALE 1:1