



- SPECIFICATIONS
1. Current Rating: 3A AC, DC
  2. Voltage Rating: 250V AC, DC
  3. Temperature Range: -25°C ~ +85°C
  4. Contact Resistance: 20mΩ Max
  5. Insulation Resistance: 1000mΩ Min
  6. Withstanding Voltage: 800V AC/minute
  7. Material: Phosphoric bronze Tin-platde
  8. Applicable Wire Sizes: AWG#22~28#

		GENERAL TOLERANCE		制图 DRAWING	深圳市富港科技有限公司			
		DIM TOL		审核 CHECK				
		X.X ±0.30		批准 APPROVAL	产品名称 TITLE	PHD (2.00) 端子	版本 REV.	A
1	初版发行	X.XX ±0.20		比例 SCALE	产品料号 PART NO.	FG-PHD-T	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°	投影 Projection	材料 MATERIAL	页次 SHEET		1/1