



SPECIFICATIONS
 Rated Current: 3.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C

Contact Material: Brass
 Contact Plating: Au or Sn Over Ni
 Insulator Material: Polyester (UL94V-0)
 Standard: PBT
 Max. Processing Temp: 230°C ± 5°C 5S



Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE ± 0.05)

			GENERAL TOLERANCE		制 图 DRAWING		深圳市富港科技有限公司			
			DIM	TOL	审 核 CHECK					
			X.X	± 0.30	批 准 APPROVAL		产品名称 TITLE	IDC刺破式连接器	版本 REV.	A
1			初版发行		比 例 SCALE		产品料号 PART NO.	FG-JN254-2xNP	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ± 3.0°		投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1