








NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 0.8
- 2.Voltage Rating: 30V AC DC
- 3.Current Rating: 0.5A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 200V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

Part No	Pin	A	B	Part No	Pin	A	B
ZX-0.8-2PLT	2	0.80	3.85	ZX-0.8-14PLT	14	10.40	13.45
ZX-0.8-3PLT	3	1.60	4.65	ZX-0.8-15PLT	15	11.20	14.25
ZX-0.8-4PLT	4	2.40	5.45	ZX-0.8-16PLT	16	12.00	15.05
ZX-0.8-5PLT	5	3.20	6.25	ZX-0.8-17PLT	17	12.80	15.85
ZX-0.8-6PLT	6	4.00	7.05	ZX-0.8-18PLT	18	13.60	16.65
ZX-0.8-7PLT	7	4.80	7.85	ZX-0.8-19PLT	19	14.40	17.45
ZX-0.8-8PLT	8	5.60	8.65	ZX-0.8-20PLT	20	15.20	18.25
ZX-0.8-9PLT	9	6.40	9.45	ZX-0.8-21PLT	21	16.00	19.05
ZX-0.8-10PLT	10	7.20	10.25	ZX-0.8-22PLT	22	16.80	19.85
ZX-0.8-11PLT	11	8.00	11.05	ZX-0.8-23PLT	23	17.60	20.65
ZX-0.8-12PLT	12	8.80	11.85	ZX-0.8-24PLT	24	18.40	21.45
ZX-0.8-13PLT	13	9.60	12.65	/	/	/	/

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-0.8-NPLT	版本 REV.	A
			.X±0.20	X°.±5°	审核 CHECK	LEO			品名 TITLE	WAFER 0.8 立贴	页次 SHEET	1/1
			.XX±0.10	X.X°.±3°	核准 APPROVAL	JOHN			客户料号 CUTM.NO.			
			.XXX±0.05	X.XX°.±1°	单位 UNITS	MM	比例 SCALE	1:1	兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			