



技术要求 Specification:

1. 材质 Material: PA66 UL94V-0:
2. 额定电流 Current rating: 1.0A AC, DC
3. 额定电压 Voltage rating: 50V AC, DC
4. 温度范围 Temperature range: -25°C to +85°C
5. 接触电阻 Contact resistance: < 30mΩ
6. 绝缘电阻 Insulation resistance: > 100MΩ
7. 耐压 Withstand voltage: 500V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

Part No	Pin	A	B	C	D
ZX-GH1.25-2PJK	2	1.25	2.00	3.75	
ZX-GH1.25-3PJK	3	2.50	3.20	5.00	
ZX-GH1.25-4PJK	4	3.75	4.30	6.25	
ZX-GH1.25-5PJK	5	5.00	4.30	7.50	6.25
ZX-GH1.25-6PJK	6	6.25	6.25	8.75	8.75
ZX-GH1.25-7PJK	7	7.50	6.25	10.00	8.75
ZX-GH1.25-8PJK	8	8.75	6.25	11.25	8.75
ZX-GH1.25-9PJK	9	10.00	6.25	12.50	8.75
ZX-GH1.25-10PJK	10	11.25	8.30	13.75	10.70
ZX-GH1.25-11PJK	11	12.50	8.30	15.00	10.70
ZX-GH1.25-12PJK	12	13.75	8.30	16.25	10.70
ZX-GH1.25-13PJK	13	15.00	8.30	17.50	10.70
ZX-GH1.25-14PJK	14	16.25	8.30	18.75	10.70
ZX-GH1.25-15PJK	15	17.50	8.30	20.00	10.70
ZX-GH1.25-16PJK	16	18.75	8.30	21.25	

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	料号 PART NO.	ZX-GH1.25-NPJK		版本 REV.	A
			.X±0.30	X.*±1°	ROSE	品名 TITLE	GH1.25MM HOUSING		页次 SHEET	1/1
			.XX±0.20		审核 CHECK	客户料号 CUTM.NO.				
			.XXX±0.10		核准 APPROVAL					
					单位 UNITS	比例 SCALE				
					MM	1:1	兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			