



SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°c to +105°c

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PBT
 Max.Processing Temp: 180°C for 30-60 seconds
 (230°C for 10 seconds)

| | | | | | | | | | |
|-----------|------------------------|-------------------|-------------------|-------|------------------|------------------|----------------------|-------------|-----|
| | | | GENERAL TOLERANCE | | 制图 DRAWING | 深圳市富港科技有限公司 | | | |
| | | | DIM | TOL | 审核 CHECK | | | | |
| | | | X.X | ±0.30 | 批准 APPROVAL | 产品名称 TITLE | 2.54 跳线帽 (开口) | 版本 REV. | A |
| 1 | | | 初版发行 | | 比例 SCALE | 产品料号 PART NO. | FG-M254-1-65-CL-B-G0 | 单位 UNITS | mm |
| 序号 No. | 变更内容 MODIFY CONTENT | 日期 MODIFY DATE | Angle | ±3.0° | 投影 Projection | 材料 MATERIAL | | 页次 SHEET | 1/1 |