



- SPECIFICATIONS
- 1、Current Rating: 2A AC, DC
 - 2、Voltage Rating: 250V AC, DC
 - 3、Temperatuer Range: -40°C ~ +105°C
 - 4、Contact Resistance: 20mΩ Max
 - 5、Insulation Resistance: 1000mΩ Min
 - 6、Withstanding Voltang: 800V AC/minute
 - 7、Material: Phosphoric bronze Tin-plated

TYPE	Dimension mm				适用线规 AWG#	Qty/Reel
	A1	B1	A2	B2		
FG-PHB-T	2.1	2.3	1.6	1.7	24-22	12000 PCS

			GENERAL TOLERANCE		制图 DRAWING		深圳市富港科技有限公司				
			DIM	TOL	审核 CHECK						
			X.X	±0.30	批准 APPROVAL		产品名称 TITLE	PHB (2.0) 端子		版本 REV.	A
1 初版发行			X.XX	±0.20	比例 SCALE		产品料号 PART NO.	FG-PHB-T		单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	投影 Projection		材料 MATERIAL			页次 SHEET	1/1