



| Part No | Pin | A | B | C |
|-----------------|-----|-------|-------|------|
| ZX-VH3.96-2PJK | 2 | 3.96 | 8.20 | 3.55 |
| ZX-VH3.96-3PJK | 3 | 7.92 | 12.10 | 7.40 |
| ZX-VH3.96-4PJK | 4 | 11.88 | 16.06 | 7.40 |
| ZX-VH3.96-5PJK | 5 | 15.84 | 20.02 | 7.40 |
| ZX-VH3.96-6PJK | 6 | 19.80 | 23.98 | 7.40 |
| ZX-VH3.96-7PJK | 7 | 23.76 | 27.94 | 7.40 |
| ZX-VH3.96-8PJK | 8 | 27.72 | 31.90 | 7.40 |
| ZX-VH3.96-9PJK | 9 | 31.68 | 35.86 | 7.40 |
| ZX-VH3.96-10PJK | 10 | 35.64 | 39.82 | 7.40 |
| ZX-VH3.96-11PJK | 11 | 39.60 | 43.78 | 7.40 |
| ZX-VH3.96-12PJK | 12 | 43.56 | 47.74 | 7.40 |

技术要求Specification:

1. 材质Material: PA66 UL94V-2(0):
2. 额定电流 Current rating:3.0A AC,DC
3. 额定电压 Voltage rating:250V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:≤0.02Ω
6. 绝缘电阻Insulation resistance:≥1000MΩ
7. 耐压Withstand voltage:1000V AC/minute
8. 塑件表面平整光洁,无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious glitches, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

| 制图 DRAWN | 变更内容 DESCRIPTION | 日期 DATE | GENERAL TOLERANCE | | 制图 DRAWING | 料号 PART NO. | ZX-VH3.96-NPJK | 版本 REV. | A |
|-------------|---------------------|------------|-------------------|--------|---------------|---|------------------|-------------|-----|
| | | | X.:±0.30 | X.:±1° | ROSE | 品名 TITLE | VH3.96MM HOUSING | 页次 SHEET | 1/1 |
| | | | X.X:±0.20 | | LEO | 客户料号 CUTM.NO. | | | |
| | | | X.XX:±0.10 | | JOHN | 兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd. | | | |
| | | | | | 单位 UNITS | MM | 比例 SCALE | 1:1 | |