


SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C ~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Housing Nylon66 UL94-V0

Circuit	Part NO.	Dimensions mm	
		A	B
2	FG-VH-2Y	3.96	8.02
3	FG-VH-3Y	7.92	11.98
4	FG-VH-4Y	11.88	15.94
5	FG-VH-5Y	15.84	19.90
6	FG-VH-6Y	19.80	23.86
7	FG-VH-7Y	23.76	27.82
8	FG-VH-8Y	27.72	31.78
9	FG-VH-9Y	31.68	35.74
10	FG-VH-10Y	35.64	39.70



			GENERAL TOLERANCE		制 图 DRAWING		深圳市富港科技有限公司			
			DIM	TOL	审 核 CHECK					
			X. X	±0.30	批 准 APPROVAL		产品名称 TITLE	VH (3.96) 单排孔座	版本 REV.	A
1 初版发行			X. XX	±0.20	比 例 SCALE		产品料号 PART NO.	FG-VH-NY	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X. XXX	±0.10	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1
			Angle	±3.0°						