



技术要求Specification:

- 1、材质Material: PA66 UL94V-0;
- 2、塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

Part No	Pin	A	B	C
ZX-SH1.0-2PJK	2	1.00	5.00	2.40
ZX-SH1.0-3PJK	3	2.00	6.00	3.40
ZX-SH1.0-4PJK	4	3.00	7.00	4.40
ZX-SH1.0-5PJK	5	4.00	8.00	5.40
ZX-SH1.0-6PJK	6	5.00	9.00	6.40
ZX-SH1.0-7PJK	7	6.00	10.00	7.40
ZX-SH1.0-8PJK	8	7.00	11.00	8.40
ZX-SH1.0-9PJK	9	8.00	12.00	9.40
ZX-SH1.0-10PJK	10	9.00	13.00	10.40
ZX-SH1.0-11PJK	11	10.00	14.00	11.40
ZX-SH1.0-12PJK	12	11.00	15.00	12.40
ZX-SH1.0-13PJK	13	12.00	16.00	13.40
ZX-SH1.0-14PJK	14	13.00	17.00	14.40
ZX-SH1.0-15PJK	15	14.00	18.00	15.40
ZX-SH1.0-16PJK	16	15.00	19.00	16.40
ZX-SH1.0-17PJK	17	16.00	20.00	17.40
ZX-SH1.0-18PJK	18	17.00	21.00	18.40
ZX-SH1.0-19PJK	19	18.00	22.00	19.40
ZX-SH1.0-20PJK	20	19.00	23.00	20.40

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE		料号 PART NO.	ZX-SH1.0-NPJK		版本 REV.	A					
			.X±0.30	X.*±1*		审核 CHECK	LEO		品名 TITLE	SH1.0MM HOUSING		页次 SHEET	1/1				
			.XX±0.20				核准 APPROVAL			JOHN			客户料号 CUTM.NO.				
			.XXX±0.10							单位 UNITS				MM	比例 SCALE		1:1