


SPECIFICATIONS

Rated Current:2.0AMP  
 Contact Resistance:20mΩMax  
 Withstand Voltage:500V AC/DC  
 Insulation Resistance:1000MΩMin  
 Operation Temperature:-40°C to +105°C

Contact Material:Brass  
 Contact Plating:Au Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PBT  
 Max.Processing Temp: 230°C±5°C 5S



			GENERAL TOLERANCE		制图 DRAWING		深圳市富港科技有限公司			
			DIM	TOL	审核 CHECK					
			X.X	±0.30	批准 APPROVAL		产品名称 TITLE	2.00 跳线帽 (闭口)	版本 REV.	A
			X.XX	±0.20	比例 SCALE		产品料号 PART NO.	FG-M200-1-50-CL-R-G1	单位 UNITS	mm
			X.XXX	±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
1	初版发行		Angle	±3.0°						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE								