



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:Phosphoric bronze Tin-plated
- 8、Applicable Wire Sizes:AWG#22~28#

GENERL TOLERANCE		制 图 DRAWING	料 号	FG-XA-T	版 本	A	
X.±0.25	X.*±2'		PART NO.		REV.		
.X±0.20	.X*±1'		审 核 CHECK	品 名	XA端子	页 次	1/1
.XX±0.15	.XX*±0.5'		核 准 APPROVAL	TITLE		SHEET	
.XXX±0.10	.XXX*±0.5'	单 位 UNITS	客 户 料 号 CUTL. NO.				
		MM	比 例 SCALE	1:1			深圳市富港科技有限公司