



NOTES:
 1. Rating:
 CQC 6A 250VAC / 6(8)A 250VAC T105/55
 8A/128A 250VAC
 UL CUL 10GPA 125VAC
 6GPA 250VAC T105/55
 VDE ENEC 6(4)A 250VAC T85/55
 KC 6(4)A 250VAC T85/55
 2. Circuit Diagram: 2P ON-OFF
 3. Terminal Strength: ≥80N
 4. Electrical life: ≥10000 cycles
 5. Withstand Voltage:
 Between all terminals: 1500VAC 1min
 Between terminals to Base: 3000VAC 1min
 Leakage Current: 1mA
 6. Current resistance: ≤50mΩ (initial)
 7. Insulation resistance: >100MΩ
 8. Body Materil: NYLON 66 94V-2°

7	底座	1	PA66		
6	弯端	1	黄铜+银合金触点	镀锡	
5	中端	1	黄铜	镀锡	
4	接触桥	1	黄铜+铜触点	镀银	
3	套管	1	铁	镀镍	
2	弹簧	1	碳素钢丝	回火	
1	按钮	1	PA66		
序号	名称	数量	材料	处理	备注

			GENERAL TOLERANCE	制图 DRAWING	深圳市富港科技有限公司						
			DIM	审核 CHECK	产品名称 TITLE		船型开关		版本 REV.	A	
			TOL	批准 APPROVAL	产品料号 PART NO.		FG-RS601A-1010013BB-6A		单位 UNITS	mm	
1			UP TO 5 ±0.20	比例 SCALE					页次 SHEET	1/1	
1			ABOVE 5 TO 30 ±0.30	投影 Projection							
序号 No.			ABOVE 30 ±0.50	材料 MATERIAL							
变更内容 MODIFY CONTENT			Angle ±5.0°								
日期 MODIFY DATE											