




SPECIFICATIONS

Current Rating: 1.0 Amps
 Withstanding Voltage: AC 500V
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Operation Temperature: -40° to +105°
 Insulator Material: Polyester (UL94V-0)
 Contact Material: Phosphor bronze
 Standard: PA6T
 Contact Plating: Gold Flash
 Max. Processing Temp: 240°C for 30-60 seconds
 (260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE: ±0.05 (TOP VIEW)



| P/N | PIN | DIM.A | DIM.B |
|--------------------|-------|--------------|------------|
| ZX-PM1.27-2-1PU-W | 2*1 | 0.00 | 1.27 |
| ZX-PM1.27-2-2PU-W | 2*2 | 1.27 | 2.54 |
| ZX-PM1.27-2-3PU-W | 2*3 | 2.54 | 3.81 |
| ZX-PM1.27-2-4PU-W | 2*4 | 3.81 | 5.08 |
| ZX-PM1.27-2-5PU-W | 2*5 | 5.08 | 6.35 |
| ZX-PM1.27-2-6PU-W | 2*6 | 6.35 | 7.62 |
| ZX-PM1.27-2-7PU-W | 2*7 | 7.62 | 8.89 |
| ZX-PM1.27-2-8PU-W | 2*8 | 8.89 | 10.16 |
| ZX-PM1.27-2-9PU-W | 2*9 | 10.16 | 11.43 |
| | | | |
| ZX-PM1.27-2-50PU-W | 2*50 | (PIN-1)x1.27 | (PIN)x1.27 |

| 制图 DRAWN | 变更内容 DESCRIPTION | 日期 DATE | GENERAL TOLERANCE | | 制图 DRAWING | 料号 PART NO. | 版本 REV. |
|-------------|---------------------|------------|-------------------|-----------|--------------------|---|--------------------|
| | | | X.±0.30 | X.*±5° | ROSE | ZX-PM1.27-2-NPU-W | A |
| | | | .X±0.20 | .X*±1° | 审核 CHECK | 品名 TITLE 1.27FH H4.3 2xNPin SMT Um PC4.8 PB4.6 6T | 页次 SHEET 1/1 |
| | | | .XX±0.10 | .XX*±0.5° | 核准 APPROVAL | 客户料号 CUTM.NO. | |
| | | | | | 单位 UNITS MM | 兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd. | |
| | | | | | 比例 SCALE 1:1 | | |