



SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
  - 2、Voltage Rating: 50V AC, DC
  - 3、Temperatuer Range:  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
  - 4、Contact Resistance:  $20\text{m}\Omega$  Max
  - 5、Insulation Resistance:  $500\text{M}\Omega$  Min
  - 6、Withstanding Voltang: 500V AC/minute
  - 7、Material: Phosphoric bronze Tin-plated
  - 8、Applicable Wire Sizes: AWG#26-32#
- Qty/Reel: 10000 PCS

|           |                        |                   |                  |                   |                   |  |                  |              |              |     |
|-----------|------------------------|-------------------|------------------|-------------------|-------------------|--|------------------|--------------|--------------|-----|
|           |                        |                   | GENEAL TOLERANCE |                   | 制 图<br>DRAWING    |  | 深圳市富港科技有限公司      |              |              |     |
|           |                        |                   | DIM              | TOL               | 审 核<br>CHECK      |  |                  |              |              |     |
|           |                        |                   | X.X              | $\pm 0.30$        | 批 准<br>APPROVAL   |  | 产品名称<br>TITLE    | ZH (1.50) 端子 | 版本<br>REV.   | A   |
| 1         |                        |                   | 初版发行             |                   | 比 例<br>SCALE      |  | 产品料号<br>PART NO. | FG-ZH-T      | 单 位<br>UNITS | mm  |
| 序号<br>No. | 变更内容<br>MODIFY CONTENT | 日期<br>MODIFY DATE | Angle            | $\pm 3.0^{\circ}$ | 投 影<br>Projection |  | 材 料<br>MATERIAL  |              | 页 次<br>SHEET | 1/1 |