



技术要求Specification:

1. 材质Material: PA66 UL94V-0:
2. 额定电流 Current rating:3.0A AC,DC
3. 额定电压 Voltage rating:250V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:≤20mΩ
6. 绝缘电阻Insulation resistance:≥1000MΩ
7. 耐压Withstand voltage:1000V AC/minute
8. 塑件表面平整光洁,无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrsbubbles, distortion, gate strain, lack of material and otherundesirable phenomena.

Part No	Pin	A	B	C	D
ZX-XH2.54-2PJK	2	2.50	5.70	3.70	3.70
ZX-XH2.54-3PJK	3	5.00	8.20	6.20	6.20
ZX-XH2.54-4PJK	4	7.50	10.70	8.70	8.70
ZX-XH2.54-5PJK	5	10.00	13.20	11.20	11.20
ZX-XH2.54-6PJK	6	12.50	15.70	13.70	13.70
ZX-XH2.54-7PJK	7	15.00	18.20	16.20	16.20
ZX-XH2.54-8PJK	8	17.50	20.70	18.70	18.70
ZX-XH2.54-9PJK	9	20.00	23.20	21.20	21.20
ZX-XH2.54-10PJK	10	22.50	25.70	23.70	23.70
ZX-XH2.54-11PJK	11	25.50	28.20	26.20	26.20
ZX-XH2.54-12PJK	12	27.50	30.70	28.70	28.70
ZX-XH2.54-13PJK	13	30.00	33.20	31.20	31.20
ZX-XH2.54-14PJK	14	32.50	35.70	33.70	33.70
ZX-XH2.54-15PJK	15	35.50	28.20	36.20	36.20
ZX-XH2.54-16PJK	16	37.50	40.70	38.70	38.70

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE	料号 PART NO.	ZX-XH2.54-NPJK	版本 REV.	A										
			.X±0.30	X.*±1°							审核 CHECK	LEO	品名 TITLE	XH2.5MM HOUSING	页次 SHEET	1/1				
			.XX±0.20														核准 APPROVAL	JOHN	客户料号 CUTM.NO.	
			.XXX±0.10																	