



技术要求Specification:

1. 材质Material: PA66 UL94V-0:
2. 额定电流 Current rating:2.0A AC,DC
3. 额定电压 Voltage rating:100V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:≤20mΩ
6. 绝缘电阻Insulation resistance:≥1000MΩ
7. 耐压Withstand voltage:800V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles.distortion, gate strain, lack of material and other undesirable phenomena.



Part No	Pin	A	B	C
ZX-PH2.0-2PJK	2	2.00	5.70	4.50
ZX-PH2.0-3PJK	3	4.00	7.70	6.50
ZX-PH2.0-4PJK	4	6.00	9.70	8.50
ZX-PH2.0-5PJK	5	8.00	11.70	10.50
ZX-PH2.0-6PJK	6	10.00	13.70	12.50
ZX-PH2.0-7PJK	7	12.00	15.70	14.50
ZX-PH2.0-8PJK	8	14.00	17.70	16.50
ZX-PH2.0-9PJK	9	16.00	19.70	18.50
ZX-PH2.0-10PJK	10	18.00	21.70	20.50
ZX-PH2.0-11PJK	11	20.00	23.70	22.50
ZX-PH2.0-12PJK	12	22.00	25.70	24.50
ZX-PH2.0-13PJK	13	24.00	27.70	26.50
ZX-PH2.0-14PJK	14	26.00	29.70	28.50
ZX-PH2.0-15PJK	15	28.00	31.70	30.50
ZX-PH2.0-16PJK	16	30.00	33.70	32.50

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING
			.X±0.30	X.*±1°	
			.XX±0.20		审核 CHECK
			.XXX±0.10		核准 APPROVAL
					单位 UNITS

ROSE		料号 PART NO.	ZX-PH2.0-NPJK	版本 REV.	A
LEO		品名 TITLE	PH2.0MM HOUSING	页次 SHEET	1/1
JOHN		客户料号 CUTM.NO.			
MM		 兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			
比例 SCALE	1:1				