



技术要求 Specification:

1. 材质 Material: PA66 UL94V-0:
2. 额定电流 Current rating: 3.0A AC, DC
3. 额定电压 Voltage rating: 250V AC, DC
4. 温度范围 Temperature range: -25°C to +85°C
5. 接触电阻 Contact resistance: ≤ 20mΩ
6. 绝缘电阻 Insulation resistance: ≥ 1000MΩ
7. 耐压 Withstand voltage: 1000V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。
Plastic surface smooth and clean, no obvious glitches, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

Part No	Pin	A	B
ZX-HA2.54-2PJK	2	2.50	5.80
ZX-HA2.54-3PJK	3	5.00	8.30
ZX-HA2.54-4PJK	4	7.50	10.80
ZX-HA2.54-5PJK	5	10.00	13.30
ZX-HA2.54-6PJK	6	12.50	15.80
ZX-HA2.54-7PJK	7	15.00	18.30
ZX-HA2.54-8PJK	8	17.50	20.80
ZX-HA2.54-9PJK	9	20.00	23.30
ZX-HA2.54-10PJK	10	22.50	25.80
ZX-HA2.54-11PJK	11	25.00	28.30
ZX-HA2.54-12PJK	12	27.50	30.80
ZX-HA2.54-13PJK	13	30.00	33.30
ZX-HA2.54-14PJK	14	32.50	35.80
ZX-HA2.54-15PJK	15	35.00	38.30
ZX-HA2.54-16PJK	16	37.50	40.80
ZX-HA2.54-17PJK	17	40.00	43.30

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING
			.X ± 0.30	X.* ± 1°	
			.XX ± 0.20		
			.XXX ± 0.10		
					单位 UNITS

ROSE
LEO
JOHN
MM
比例 SCALE
1:1

料号 PART NO.	ZX-HA2.54-NPJK	版本 REV.	A
品名 TITLE	HA2.5MM HOUSING	页次 SHEET	1/1
客户料号 CUTM.NO.			
 兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			