



SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperatuer Range: -40°C ~ +105°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100mΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Housing Nylon66 UL94-V0(2)

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	FG-1.25-2Y	1.25	4.25	2.95
3	FG-1.25-3Y	2.50	5.50	4.20
4	FG-1.25-4Y	3.75	6.75	5.45
5	FG-1.25-5Y	5.00	8.00	6.70
6	FG-1.25-6Y	6.25	9.25	7.95
7	FG-1.25-7Y	7.50	10.50	9.20
8	FG-1.25-8Y	8.75	11.75	10.45
9	FG-1.25-9Y	10.00	13.00	11.70
10	FG-1.25-10Y	11.25	14.25	12.95
11	FG-1.25-11Y	12.50	15.50	14.20
12	FG-1.25-12Y	13.75	16.75	15.45
13	FG-1.25-13Y	15.00	18.00	16.70
14	FG-1.25-14Y	16.25	19.25	17.95
15	FG-1.25-15Y	17.50	20.50	19.20

		GENERAL TOLERANCE		制图 DRAWING	深圳市富港科技有限公司			
		DIM	TOL	审核 CHECK				
		X.X	±0.30	批准 APPROVAL	产品名称 TITLE	1.25 单排 孔座	版本 REV.	A
1	初版发行	X.XX	±0.20	比例 SCALE	产品料号 PART NO.	FG-1.25-NY	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°	投影 Projection	材料 MATERIAL		页次 SHEET	1/1