






SPECIFICATIONS

Current Rating: 3Amps  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Withstanding Voltage: AC 1000V  
 Operation Temperature: -40°to+105°  
 Contact Material: Brass  
 Insulator Material: Polyester(UL 94V-0)  
 Contact plating: Gold Flash  
 Standard: PBT  
 Max.Processing Temp: 200°C for30-60seconds  
 (220°C for5seconds)



RECOMMEND P.C.B LAYOUT  
 PCB TOLERANCE:±0.05 (TOP VIEW)



P/N	PIN	DIM.A	DIM.B
ZX-IDC2.54-2-3PZN	2*3	5.08	26.92
ZX-IDC2.54-2-4PZN	2*4	7.62	29.46
ZX-IDC2.54-2-5PZN	2*5	10.16	32.00
ZX-IDC2.54-2-6PZN	2*6	12.70	34.54
ZX-IDC2.54-2-7PZN	2*7	15.24	37.08
ZX-IDC2.54-2-8PZN	2*8	17.78	39.60
ZX-IDC2.54-2-10PZN	2*10	22.86	44.70
ZX-IDC2.54-2-12PZN	2*12	27.94	49.78
ZX-IDC2.54-2-13PZN	2*13	30.48	52.30
ZX-IDC2.54-2-15PZN	2*15	35.56	57.40
ZX-IDC2.54-2-17PZN	2*17	40.64	62.50
ZX-IDC2.54-2-20PZN	2*20	48.26	70.10
ZX-IDC2.54-2-25PZN	2*25	60.96	82.85
ZX-IDC2.54-2-30PZN	2*30	73.66	95.40
ZX-IDC2.54-2-32PZN	2*32	78.74	100.48

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING
			.X±0.30	X°.±5°	
			.XX±0.25	X.X°.±1°	审核 CHECK
			.XXX±0.20	X.XX°.±0.5°	核准 APPROVAL
					单位 UNITS

ROSE  
LEO  
JOHN

料号 PART NO.	ZX-IDC2.54-2-NPZN	版本 REV.	A
品名 TITLE	2.54DC2-NPin H17 180度 PC3.8 PBT	页次 SHEET	1/1
客户料号 CUTM.NO.			
比例 SCALE	1:1		

兆星精密电子(深圳)有限公司  
 ShenZhen ZhaoXing Precision electronics Co., Ltd.