



SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Housing Nylon66 UL94-V0(2)

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	FG-PHB-2x2Y	2.00	7.00	4.70
3	FG-PHB-2x3Y	4.00	9.00	6.70
4	FG-PHB-2x4Y	6.00	11.00	8.70
5	FG-PHB-2x5Y	8.00	13.00	10.70
6	FG-PHB-2x6Y	10.00	15.00	12.70
7	FG-PHB-2x7Y	12.00	17.00	14.70
8	FG-PHB-2x8Y	14.00	19.00	16.70
9	FG-PHB-2x9Y	16.00	21.00	18.70
10	FG-PHB-2x10Y	18.00	23.00	20.70
11	FG-PHB-2x11Y	20.00	25.00	22.70
12	FG-PHB-2x12Y	22.00	27.00	24.70
13	FG-PHB-2x13Y	24.00	29.00	26.70
14	FG-PHB-2x14Y	26.00	31.00	28.70
15	FG-PHB-2x15Y	28.00	33.00	30.70
16	FG-PHB-2x16Y	30.00	35.00	32.70
17	FG-PHB-2x17Y	32.00	37.00	34.70
18	FG-PHB-2x18Y	34.00	39.00	36.70
19	FG-PHB-2x19Y	36.00	41.00	38.70
20	FG-PHB-2x20Y	38.00	43.00	40.70
21	FG-PHB-2x21Y	40.00	45.00	42.70
22	FG-PHB-2x22Y	42.00	47.00	44.70
30	FG-PHB-2x30Y	58.00	63.00	60.70

			GENERAL TOLERANCE		制图 DRAWING		深圳市富港科技有限公司			
			DIM	TOL	审核 CHECK					
			X.X	±0.30	批准 APPROVAL		产品名称 TITLE	PHB (2.0) 双排孔座	版本 REV.	A
1			初版发行		比例 SCALE		产品料号 PART NO.	FG-PHB-2xNY	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°		投影 Projection		材料 MATERIAL		页次 SHEET	1/1