


SEC:A-A



SEC:B-B

Technical Index:

1. Temperature range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. Rated voltage: 250V DC/AC.
3. Rated current: 3.0A DC/AC.
4. Contact resistance: $\leq 20\text{m}\Omega$.
5. Dielectric withstanding voltage: 800V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.
7. Apply to gauge: AWG#24~#28.

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE	
			X.±0.30	X.°±5°
			.X±0.25	.X°±1°
			.XX±0.15	

序号	品名	材质			
1	端子	Phosphor Bronze Bright tin plated			
料号 PART NO.	ZX-PHB2.0-2-DZ	版本 REV.	A		
品名 TITLE	PHB2.0公共端子	页次 SHEET	1/1		
客户料号 CUTM.NO.					
		兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			

制图
DRAWING ROSE
审核
CHECK LEO
核准
APPROVAL JOHN
单位
UNITS MM
比例
SCALE 1:1