



SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩMax
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩMin
 Operation Temperature:-40°c to +105°c

Contact Material: Brass
 Contact Plating: Au Over Ni
 Insulator Material: Polyester(UL94V-0)
 Standard: PA66
 Max.Processing Temp: 180°C for 30-60 seconds
 (230°C for 10 seconds)



			GENE RL TOL ERANCE	制 图 DRAWING	深圳市富港科技有限公司				
			DIM TOL	审 核 CHECK	产品名称 TITLE	2.54 跳线帽 红色 (开口 加长带柄)	版本 REV.	A	
			X.X ±0.30	批 准 APPROVAL	产品料号 PART NO.	FG-M254-1-135-0P-R-G1	单 位 UNITS	mm	
1	初版发行		X.XX ±0.20	投 影 SCALE	材 料 MATERIAL		页 次 SHEET	1/1	
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°	投影 Projection					