



**SPECIFICATIONS**

- 1、Current Rating: 4A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:Nylon66,UL94V-0

编 号	尺寸 (mm)	
	A	B
2510-2Y	2.54	5.68
2510-3Y	5.08	8.22
2510-4Y	7.62	10.76
2510-5Y	10.16	13.30
2510-6Y	12.70	15.84
2510-7Y	15.24	18.38
2510-8Y	17.78	20.92
2510-9Y	20.32	23.46
2510-10Y	22.86	26.00
2510-11Y	25.40	28.54
2510-12Y	27.94	31.08

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制 图 DRAWING	料 号 PART NO.	FG-2510-NY	版本 REV.	A							
			X.±0.25	X.*±2°						审 核 CHECK	品 名 TITLE	页次 SHEET	1/1			
			.X±0.20	.X*±1°										核 准 APPROVAL	客户料号 CUTM. NO.	
			.XX±0.15	.XX*±0.5°												
.XXX±0.10	.XXX*±0.5°	单 位 UNITS	MM	比 例 SCALE	1:1											