



Part No	Pin	A	B	Part No	Pin	A	B
ZX-0.8-2PWT	2	0.80	3.85	ZX-0.8-14PWT	14	10.40	13.45
ZX-0.8-3PWT	3	1.60	4.65	ZX-0.8-15PWT	15	11.20	14.25
ZX-0.8-4PWT	4	2.40	5.45	ZX-0.8-16PWT	16	12.00	15.05
ZX-0.8-5PWT	5	3.20	6.25	ZX-0.8-17PWT	17	12.80	15.85
ZX-0.8-6PWT	6	4.00	7.05	ZX-0.8-18PWT	18	13.60	16.65
ZX-0.8-7PWT	7	4.80	7.85	ZX-0.8-19PLT	19	14.40	17.45
ZX-0.8-8PWT	8	5.60	8.65	ZX-0.8-20PWT	20	15.20	18.25
ZX-0.8-9PWT	9	6.40	9.45	ZX-0.8-21PWT	21	16.00	19.05
ZX-0.8-10PWT	10	7.20	10.25	ZX-0.8-22PWT	22	16.80	19.85
ZX-0.8-11PWT	11	8.00	11.05	ZX-0.8-23PWT	23	17.60	20.65
ZX-0.8-12PWT	12	8.80	11.85	ZX-0.8-24PWT	24	18.40	21.45
ZX-0.8-13PWT	13	9.60	12.65	/	/	/	/

NOTES:  
 1.BASE: LCP  
 2.PIN: Brass  
 3.Solder Tab: Brass

SPECIFICATIONS:  
 1.Spacing: 0.8  
 2.Voltage Rating: 30V AC DC  
 3.Current Rating: 0.5A AC DC  
 4.Insulation Resistance: 100MΩ Min  
 5.Contact Resistance: 20mΩ Max  
 6.Withstanding voltage: 200V AC 1/Minute  
 7.Temperatuer Range: -25℃ ~+ 85℃

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE	料号 PART NO.	ZX-0.8-NPWT	版本 REV.	A
			.X±0.20	X'':±5°						
			.XX±0.10	X.X':±3°	核准 APPROVAL	JOHN	客户料号 CUTM.NO.			
			.XXX±0.05	X.XX':±1°	单位 UNITS	MM	比例 SCALE	1:1		


**兆星精密电子（深圳）有限公司**  
 ShenZhen ZhaoXing Precision electronics Co., Ltd.