



A		B		C		D		E	
REV.	DESCRIPTION				ECN NO.	NAME	DATE		

1




可打K脚, 50k起订

2

3

4




技术要求:

1. 塑件材料: PA66(UL-94V-0)
2. 接触件: 黄铜镀锡
3. 接触电阻: $\leq 10m\Omega$
4. 绝缘电阻: $\geq 100M\Omega$
5. 额定电压: 250V AC DC
6. 额定电流: 2.0A AC DC
7. 耐压: 能承受 1000V AC/Minute
8. 工作温度: $-25^{\circ}\sim+85^{\circ}$
9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 $235^{\circ}\pm 5^{\circ}$, 时间 2.5 ± 0.5 秒
10. 铅和镉等六大有害物质含量要符合环保要求.

Part No	Pin	A	B
B2B-XH-A-2PZZ	2	2.50	7.50
B2B-XH-A-3PZZ	3	5.00	10.00
B2B-XH-A-4PZZ	4	7.50	12.50
B2B-XH-A-5PZZ	5	10.00	15.00
B2B-XH-A-6PZZ	6	12.50	17.50
B2B-XH-A-7PZZ	7	15.00	20.00
B2B-XH-A-8PZZ	8	17.50	22.50
B2B-XH-A-9PZZ	9	20.00	25.00
B2B-XH-A-10PZZ	10	22.50	27.50
B2B-XH-A-11PZZ	11	25.00	30.00
B2B-XH-A-12PZZ	12	27.50	32.50
B2B-XH-A-13PZZ	13	30.00	35.00
B2B-XH-A-14PZZ	14	32.50	37.50
B2B-XH-A-15PZZ	15	35.00	40.00
B2B-XH-A-16PZZ	16	37.50	42.50
B2B-XH-A-17PZZ	17	40.00	45.00
B2B-XH-A-18PZZ	18	42.50	47.50
B2B-XH-A-19PZZ	19	45.00	50.00
B2B-XH-A-20PZZ	20	47.50	52.50

5



2	端子Contact	黄铜	N*1	电镀(锡): 整个表面镀底镍 30u"MIN, 再镀锡 80u"MIN
1	基座Wafer	PA66(UL94V-0)	1	白色
序号	名称	材料	数量	备注

GENERAL TOLERANCE	
DIM.	TOL.
.x	±0.20
.xx	±0.10
.xxx	±0.05
GENERAL ANGLE:	
.x°	±2.0°
.xx°	
.xxx°	

DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					
TITLE: WAFER XH2.54MM 直针					
DWG. NO.: B2B-XH-A-XPZZ			CHECKED: MAX		
PART NO.: B2B-XH-A-XPZZ			DRAWN: ELLA		
UNIT:	SCALE:	SHEET:	DWG. SIZE:	LAYER:	APPROVED: WILL
mm	none	1 of 1	A4	bxconn	

BXCONN®