




| 标记 MARK                       |                                   | ECN编号/变更内容<br>ECN NO./DEFINITION |                             | 修改 REVISION        |                | 日期 DATE |        | 核准 APPROVE |        |
|-------------------------------|-----------------------------------|----------------------------------|-----------------------------|--------------------|----------------|---------|--------|------------|--------|
| High<br>photosynthesis<br>(%) | The female<br>seat height<br>(H1) | The male<br>seat height<br>(H2)  | insertion<br>height<br>(H3) | No. of<br>Contacts | Dimension (mm) |         |        |            |        |
|                               |                                   |                                  |                             |                    | A±0.10         | B±0.10  | C±0.10 | D±0.10     | E±0.10 |
| 3.0                           | 2.2                               | 0.8                              | 1.6                         | 6                  | 4.20           | 1.00    | 2.90   | 2.00       |        |
| 3.5                           | 2.2                               | 1.3                              | 1.6                         | 8                  | 4.70           | 1.50    | 3.40   | 2.50       |        |
| 4.0                           | 3.0                               | 1.6                              | 1.9                         | 10                 | 5.20           | 2.00    | 3.90   | 3.00       |        |
| 4.5                           | 3.5                               | 1.9                              | 1.9                         | 12                 | 5.70           | 2.50    | 4.40   | 3.50       |        |
| 5.0                           | 3.0/4.0                           | 2.0/1.0                          | 1.9                         | 14                 | 6.20           | 3.00    | 4.90   | 4.00       |        |
| 5.5                           |                                   |                                  | 1.9                         | 16                 | 6.70           | 3.50    | 5.40   | 4.50       |        |
| 6.0                           | 4.0                               | 2.0                              | 1.9                         | 18                 | 7.20           | 4.00    | 5.90   | 5.00       |        |
| 6.5                           | 4.5                               | 2.0                              | 1.9                         | 20                 | 7.70           | 4.50    | 6.40   | 5.50       | 4.00   |
| 7.0                           | 3.0                               | 4.0                              | 1.9                         | 22                 | 8.20           | 5.00    | 6.90   | 6.00       |        |
| 7.5                           | 3.5                               | 4.0                              | 1.9                         | 24                 | 8.70           | 5.50    | 7.40   | 6.50       |        |
| 8.0                           | 4.0                               | 4.0                              | 1.9                         | 26                 | 9.20           | 6.00    | 7.90   | 7.00       |        |
| 8.5                           | 4.5                               | 4.0                              | 1.9                         | 28                 | 9.70           | 6.50    | 8.40   | 7.50       |        |
|                               |                                   |                                  |                             | 30                 | 10.20          | 7.00    | 8.90   | 8.00       |        |
|                               |                                   |                                  |                             | 32                 | 10.70          | 7.50    | 9.40   | 8.50       |        |
|                               |                                   |                                  |                             | 34                 | 11.20          | 8.00    | 9.90   | 9.00       |        |
|                               |                                   |                                  |                             | 36                 | 11.70          | 8.50    | 10.40  | 9.50       |        |
|                               |                                   |                                  |                             | 38                 | 12.20          | 9.00    | 10.90  | 10.00      |        |
|                               |                                   |                                  |                             | 40                 | 12.70          | 9.50    | 11.40  | 10.50      | 8.00   |
|                               |                                   |                                  |                             | 50                 | 15.20          | 12.00   | 13.90  | 13.00      |        |
|                               |                                   |                                  |                             | 60                 | 17.70          | 14.50   | 16.40  | 15.50      |        |
|                               |                                   |                                  |                             | 70                 | 20.20          | 17.00   | 18.90  | 18.00      |        |
|                               |                                   |                                  |                             | 80                 | 22.70          | 19.50   | 21.40  | 20.50      |        |
|                               |                                   |                                  |                             | 100                | 27.70          | 24.50   | 26.40  | 25.50      |        |

技术指标:

1. 工作温度: -25°C ~ +85°C
2. 额定电流: 0.5A Max
2. 接触电阻: 60mΩ Max
3. 绝缘阻抗: 800MΩ Min
4. 耐电压: 500V AC/1minute

|    |    |      |       |    |
|----|----|------|-------|----|
| 2  | 端子 | 铜    | 镀金    |    |
| 1  | 基座 | PA9T | 黑色    | 公座 |
| 序号 | 品名 | 材质   | 电镀/颜色 | 备注 |

|   |               |               |   |   |
|---|---------------|---------------|---|---|
|  深圳市虹成电子有限公司<br>GENERAL TOLERANCES<br>(UNLESS SPECIFIED) | 品名<br>TITLE   |               | 板对板   |   |
|   | 料号<br>PART NO |               | HC-BTB-0.5-2x30P-GH10-W   |   |
| 比列<br>SCALE   | 1:1           |               |  |   |
| 单位<br>UNIT  | MM            | 制图<br>DRAW    | AhYe  |  |
| 张数<br>PART NO   | 1 OF 1        | 审核<br>CHECKED | 夏操云   |   |
| 版本<br>REV   | A             | 批准<br>APPROVE | 赵亮亮   |   |