



标记 MARK		ECN编号/变更内容 ECN NO./DEFINITION		修改 REVISE	日期 DATE	核准 APPROVE		
High photosynthesis (H)	The female seat height (H1)	The male seat height (H2)	Insertion height (H3)	No. of Contacts	Dimension (mm)			
					A±0.10	B±0.10	C±0.10	E±0.10
3.0	2.2	0.8	1.6	6	4.20	1.00	2.90	2.06
3.5	2.2	1.3	1.6	8	4.70	1.50	3.40	2.56
4.0	3.0	1.6	1.9	10	5.20	2.00	3.90	3.06
4.5	3.5	1.9	1.9	12	5.70	2.50	4.40	3.56
5.0	3.0/4.0	2.0/1.0	1.9	14	6.20	3.00	4.90	4.06
5.5	3.5/4.5	2.0/1.0	1.9	16	6.70	3.50	5.40	4.56
6.0	4.0	2.0	1.9	18	7.20	4.00	5.90	5.06
6.5	4.5	2.0	1.9	20	7.70	4.50	6.40	5.56
7.0	3.0	4.0	1.9	22	8.20	5.00	6.90	6.06
7.5	3.5	4.0	1.9	24	8.70	5.50	7.40	6.56
8.0	4.0	4.0	1.9	26	9.20	6.00	7.90	7.06
8.5	4.5	4.0	1.9	28	9.70	6.50	8.40	7.56
				30	10.20	7.00	8.90	8.06
				32	10.70	7.50	9.40	8.56
				34	11.20	8.00	9.90	9.06
				36	11.70	8.50	10.40	9.56
				38	12.20	9.00	10.90	10.06
				40	12.70	9.50	11.40	10.56
				50	15.20	12.00	13.90	13.06
				60	17.70	14.50	16.40	15.56
				70	20.20	17.00	18.90	18.06
				80	22.70	19.50	21.40	20.56
				100	27.70	24.50	26.40	25.56

技术指标:

1. 工作温度: -25°C ~ +85°C
2. 额定电流: 0.5A Max
2. 接触电阻: 60mΩ Max
3. 绝缘阻抗: 800MΩ Min
4. 耐电压: 500V AC/1minute

2	端子	铜	镀金	
1	基座	PA9T	黑色	母座
序号	品名	材质	电镀/颜色	备注


深圳市虹成电子有限公司
 品名 TITLE: 板对板
 料号 PART NO: HC-BTB-0.5-2x50P-MH40-W
 GENERAL TOLERANCES (UNLESS SPECIFIED): 比列 SCALE: 1:1
 .X ±0.20 .X' ±1.0' 单位 UNIT: MM 制图 DRAW: AhYe
 .XX ±0.10 .XX' ±0.5' 张数 PART NO: 1 OF 1 审核 CHECKED: 夏操云
 .XXX ±0.05 .XXX' ±0.2' 版本 REV: A 批准 APPROVE: 赵亮亮

