



ASSEMBLY

标记 MARK		ECN编号/变更内容 ECN NO/DEFINITION		修改 REVISE	日期 DATE	核准 APPROVE			
High photosynthesis (H)	The female seat height (H1)	The male seat height (H2)	Insertion height (H3)	No. of Contacts	Dimension (mm)				
					A±0.10	B±0.10	C±0.10	D±0.10	E±0.10
4.0	3.0	1.0	1.9	6	4.30	1.60	3.40	2.60	4.00
4.5	3.5	1.0	1.9	8	5.10	2.40	4.20	3.40	
5.0	3.0/4.0	2.0/1.0	1.9	10	5.90	3.20	5.00	4.20	
5.5	3.5/4.5	2.0/1.0	1.9	12	6.70	4.00	5.80	5.00	
6.0	4.0	2.0	1.9	14	7.50	4.80	6.60	5.80	
6.5	4.5	2.0	1.9	16	8.30	5.60	7.40	6.60	
7.0	3.0	4.0	1.9	18	9.10	6.40	8.20	7.40	
7.5	3.5	4.0	1.9	20	9.90	7.20	9.00	8.20	
8.0	4.0	4.0	1.9	22	10.70	8.00	9.80	9.00	
8.5	4.5	4.0	1.9	24	11.50	8.80	10.60	9.80	
				26	12.30	9.60	11.40	10.60	8.00
				28	13.10	10.40	12.20	11.40	
				30	13.90	11.20	13.00	12.20	
				32	14.70	12.00	13.80	13.00	
				34	15.50	12.80	14.60	13.80	
				36	16.30	13.60	15.40	14.60	
				38	17.10	14.40	16.20	15.40	
				40	17.90	15.20	17.00	16.20	

技术指标:

1. 工作温度: -25°C ~ +85°C
2. 额定电流: 0.5A Max
2. 接触电阻: 60mΩ Max
3. 绝缘阻抗: 800MΩ Min
4. 耐电压: 500V AC/1minute

2	端子	铜	镀金	
1	基座	PA9T	黑色	公座
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品名 TITLE	板对板	
			料号 PART NO	HC-BTB-0.8-2x14P-GH10-W	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比列 SCALE	1:1		
.X ±0.20	.X' ±1.0'	单位 UNIT	MM		
.XX ±0.10	.XX' ±0.5'	张数 PART NO	1 OF 1	制图 DRAW	AhYe
.XXX ±0.05	.XXX' ±0.2'	版本 REV	A	审核 CHECKED	夏操云
			批准 APPROVE	赵亮亮	

