





SYMBOL DEFINITION						MISSING SYMBOLS																				
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.						DWS STATUS						ZONE		REVISION HISTORY				AUTH		DR		AP/D				
						DATE	STG	REV	N/P	CHG									DR	1	2					
TOTAL NO OF INSPECTIONS REQUIRED						NO MISSING SYMBOL NUMBER						05N003		R	01	-	-	ALL PARTS - REDRAWN TO PD				246857		JBR	RCH	JDY
												21DE06		R	02	-	-	MATERIAL FOR P/N 12146576 AND 12146501 WAS PW3639285 MATERIAL FOR P/N 12124587,12124582, 12089307,12089040 WAS P1519285				282294		TMF	TMF	TM
LAST NO. USED						6																				




TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 104
SAME AS TYPE 102
EXCEPT AS SHOWN



TYPE 101




TYPE 105
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 106
SAME AS TYPE 105
EXCEPT AS SHOWN

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- "PXX" INDICATES "P" PLUS LAST TWO DIGITS OF MAKE DIE
SERIES NUMBER (PO1, PO2, PO3, ETC).
- TERMINAL DESIGNED FOR 3MM² CABLE.
TERMINAL IS RATED AT 20 AMPERES. DO NOT EXCEED
RATED CURRENT.



DWS TYPE		PART DRAWING	
STYLE			
VOLUME 1047		DISTR CODE	
ROUTING		6900	
UNLESS OTHERWISE SPECIFIED		THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS MODIFIED BY THE M-SCS-100 DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE RATINGS OF FEATURES MAY BE BASED SEPARATELY PERMITS OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS		REFERENCE	
THIRD ANGLE PROJECTION		DO NOT SCALE	
USE MATH DATA			

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DR	
APVD1 J.GAVALDON	05N003
APVD2 R.CHACON	05N003
APVD3 J.DEL VAL	07N003
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEE CHART	
DRAWING NAME TAXI TERM M W/P I SEALED TANG	
DRAWING NUMBER 12010088	
SIZE A0	SCALE 10:1
FRAME NO 1	SHEET NO 1 OF 4
STG R	REV 02

(4) PROCESS SENSITIVE DIMENSION		CHART D	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED		FROM 0 TO 12 TOLERANCE UNLESS OTHERWISE SPECIFIED ±0.1 ANGULAR TOLERANCE 22°	

12146576	R	B2	-	0.320X36.53	M3639285	0.35-0.22	1.86	23	102	2.20	○
12146501	R	B2	-	0.320X36.53	M3639285	0.8-0.5	3.11	19	104	3.00	○
12124587	R	B2	-	0.320X36.53	M1574285	SEE NOTE 3	3.96	11	106	4.60	○
12124582	R	B2	-	0.320X36.53	M1574285	2.0-1.0	3.96	15	105	3.60	○
12089307	R	B2	-	0.320X36.53	M1574285	0.35-0.22	1.86	23	102	2.20	○
12089306	R	B	OBSOLETE	0.320X36.53	P-1519285	SEE NOTE 3	3.96	11	103	4.60	○
12089305	R	B	OBSOLETE	0.320X36.53	P-1519285	2.0-1.0	3.96	15	101	3.60	○
12089040	R	C2	-	0.320X36.53	M1574285	0.8-0.5	3.11	19	104	3.00	○
PART NO	STG	REV	N/P	STATUS	MAT'L SIZE	MAT'L SPEC	CABLE SIZE (MM ²)	MAX. CABLE DIA.	I.D.NO.	TYPE	E±0.4