



Recommended
P.C.B.layout



ASSEMBLY

标记 MARK	ECN编号/变更内容 ECN NO/DEFINITION			修改 REVISE	日期 DATE	核准 APPROVE			
	Dimension (mm)								
High photosynthesis (H)	The female seat height (H1)	The male seat height (H2)	Insertion height (H3)	NO. of Contacts	A±0.10	B±0.10	C±0.10	D±0.10	E±0.10
4.0	3.0	1.0	1.9	6	4.30	1.60	3.40	2.66	
4.5	3.5	1.0	1.9	8	5.10	2.40	4.20	3.46	
5.0	3.0/4.0	2.0/1.0	1.9	10	5.90	3.20	5.00	4.26	
5.5	3.5/4.5	2.0/1.0	1.9	12	6.70	4.00	5.80	5.06	
6.0	4.0	2.0	1.9	14	7.50	4.80	6.60	5.86	
6.5	4.5	2.0	1.9	16	8.30	5.60	7.40	6.66	
7.0	3.0	4.0	1.9	18	9.10	6.40	8.20	7.46	4.00
7.5	3.5	4.0	1.9	20	9.90	7.20	9.00	8.26	
8.0	4.0	4.0	1.9	22	10.70	8.00	9.80	9.06	
8.5	4.5	4.0	1.9	24	11.50	8.80	10.60	9.86	
				26	12.30	9.60	11.40	10.66	
				28	13.10	10.40	12.20	11.46	
				30	13.90	11.20	13.00	12.26	
				32	14.70	12.00	13.80	13.06	8.00
				34	15.50	12.80	14.60	13.86	
				36	16.30	13.60	15.40	14.66	
				38	17.10	14.40	16.20	15.46	
				40	17.90	15.20	17.00	16.26	

技术指标:

1. 工作温度: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
2. 额定电流: 0.5A Max
2. 接触电阻: $60\text{m}\Omega$ Max
3. 绝缘阻抗: $800\text{M}\Omega$ Min
4. 耐电压: 500V AC/1minute

2	端子	铜	镀金	
1	基座	PA9T	黑色	母座
序号	品名	材质	电镀/颜色	备注

 深圳市虹成电子有限公司 GENERAL TOLERANCES (UNLESS SPECIFIED)	品名 TITLE		板对板	
	料号 PART NO		HC-BTB-0.8-2x8P-MH40-W	
比列 SCALE	1:1			
单位 UNIT	MM			
张数 PART NO	1 OF 1	制图 DRAW	AhYe	
版本 REV	A	审核 CHECKED	夏操云	
		批准 APPROVE	赵亮亮	