



| 标记 MARK | | ECN编号/变更内容 ECN NO./DEFINITION | | 修改 REVISE | | 日期 DATE | | 核准 APPROVE | |
|-------------------------|-----------------------------|-------------------------------|-----------------------|-----------------|----------------|---------|--------|------------|--------|
| High photosynthesis (H) | The female seat height (H1) | The male seat height (H2) | Insertion height (H3) | No. of Contacts | Dimension (mm) | | | | |
| | | | | | A±0.10 | B±0.10 | C±0.10 | D±0.10 | E±0.10 |
| 3.0 | 2.2 | 0.8 | 1.6 | 6 | 4.20 | 1.00 | 2.90 | 2.06 | |
| 3.5 | 2.2 | 1.3 | 1.6 | 8 | 4.70 | 1.50 | 3.40 | 2.56 | |
| 4.0 | 3.0 | 1.6 | 1.9 | 10 | 5.20 | 2.00 | 3.90 | 3.06 | |
| 4.5 | 3.5 | 1.9 | 1.9 | 12 | 5.70 | 2.50 | 4.40 | 3.56 | |
| 5.0 | 3.0/4.0 | 2.0/1.0 | 1.9 | 14 | 6.20 | 3.00 | 4.90 | 4.06 | |
| 5.5 | | | 1.9 | 16 | 6.70 | 3.50 | 5.40 | 4.56 | |
| 6.0 | 3.5/4.5 | 2.0/1.0 | 1.9 | 18 | 7.20 | 4.00 | 5.90 | 5.06 | 4.00 |
| 6.5 | 4.5 | 2.0 | 1.9 | 20 | 7.70 | 4.50 | 6.40 | 5.56 | |
| 7.0 | 3.0 | 4.0 | 1.9 | 22 | 8.20 | 5.00 | 6.90 | 6.06 | |
| 7.5 | 3.5 | 4.0 | 1.9 | 24 | 8.70 | 5.50 | 7.40 | 6.56 | |
| 8.0 | 4.0 | 4.0 | 1.9 | 26 | 9.20 | 6.00 | 7.90 | 7.06 | |
| 8.5 | 4.5 | 4.0 | 1.9 | 28 | 9.70 | 6.50 | 8.40 | 7.56 | |
| | | | | 30 | 10.20 | 7.00 | 8.90 | 8.06 | |
| | | | | 32 | 10.70 | 7.50 | 9.40 | 8.56 | |
| | | | | 34 | 11.20 | 8.00 | 9.90 | 9.06 | 8.00 |
| | | | | 36 | 11.70 | 8.50 | 10.40 | 9.56 | |
| | | | | 38 | 12.20 | 9.00 | 10.90 | 10.06 | |
| | | | | 40 | 12.70 | 9.50 | 11.40 | 10.56 | |

技术指标:

1. 工作温度: -25°C ~ +85°C
2. 额定电流: 0.5A Max
2. 接触电阻: 60mΩ Max
3. 绝缘阻抗: 800MΩ Min
4. 耐电压: 500V AC/1minute

| | | | | |
|----|----|------|-------|----|
| 2 | 端子 | 铜 | 镀金 | |
| 1 | 基座 | PA9T | 黑色 | 母座 |
| 序号 | 品名 | 材质 | 电镀/颜色 | 备注 |


深圳市虹成电子有限公司
 品名 TITLE: 板对板
 料号 PART NO: HC-BTB-0.5-2x5P-MH22-W
 GENERAL TOLERANCES (UNLESS SPECIFIED): 比列 SCALE: 1:1
 .X ±0.20 .X' ±1.0' 单位 UNIT: MM 制图 DRAW: AhYe
 .XX ±0.10 .XX' ±0.5' 张数 PART NO: 1 OF 1 审核 CHECKED: 夏操云
 .XXX ±0.05 .XXX' ±0.2' 版本 REV: A 批准 APPROVE: 赵亮亮

