

A

B


C

D

E

REV.	DESCRIPTION	ECN NO.	NAME	DATE

Pin Number	Signal Name
1	VBUS
2	D-
3	D+
4	ID
5	GND



规格说明: Specifications:

电气特性: Electrical:





1. 额定电流: Current Rating
1.0A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
50 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:
300 V AC For one minuter
5. 绝缘阻抗: Insulation Resistance:
100MEGA ohms MIN

原材料: Raw material:



1. 塑胶: Plastic cement:
Hing Temperature Thermoplastics,
LCP Black/Nature
2. 端子: Contact: Copper Alloy C5191/C2680
3. 外壳: Shell: Copper Alloy C2680

电镀: Electroplate:

1. 端子: Contact: Plated Gold in Mating Area;
Tin On Solder Talls
2. 外壳: Shell:
Nickel Plating



RECOMMENDED PCB LAYOUT

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			 
DIM.	TOL.	TITLE: MINI USB 5P/F180°DIP B型(直尖脚)			
x.	±0.30	DWG. NO.: USB-MINI-ZJ94		CHECKED: MAX	
x.x	±0.20	PART NO.: USB-MINI-ZJ94		DRAWN: ELLA	
x.xx	±0.10	UNIT: mm		APPROVED: WILL	
GENERAL ANGLE:		SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn
x.°	±5.0°				
x.x°	±2.0°				
x.xx°					