



MAPX	MODIFICATION	DATE

规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating  
1.5A/contact terminal
2. 额定电压: Voltage Rating  
30V DC
3. 接触阻抗: Contact Resistance  
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:  
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:  
1000MEGA ohms MIN

物理性能: Mechanical:

1. 插拔力: Connector Mate and Unmate Force  
Mate force: 3.57kgf (MAX)  
Unmate force: 1.02kgf (MIN)
2. 端子保持力: Terminal Retention  
1.0kgf (MIN)

原材料: Material:

1. 塑胶: Housing:  
Hing Temperature Thermoplastics,
2. 端子: Contact: Copper Alloy C2680
3. 外壳: Shell: Copper Alloy C2680/SPCC

电镀: Finish:

1. 端子: Contact: Plated Gold in Mating Area;  
Tin On Solder Talls  
端子四周镀50U" (MIN) 锡, 镀金区域镀100-200U" 镀金1U"
2. 外壳: Shell:  
铜壳四周镀80U" (MIN) 锡  
Nickel Plating

<p>产品图 PRODUCT CHART DWG</p> <p>公差一览表 TOLERANCE UNLESS OTHERWISE</p> <table border="1"> <tr> <td>X</td> <td>±0.15</td> <td>.X</td> <td>±5°</td> </tr> <tr> <td>X</td> <td>±0.10</td> <td>.X</td> <td>±2°</td> </tr> <tr> <td>XX</td> <td>±0.05</td> <td>.XX</td> <td>±1°</td> </tr> <tr> <td>XXX</td> <td>±0.03</td> <td>.XXX</td> <td>±0.5°</td> </tr> </table>				X	±0.15	.X	±5°	X	±0.10	.X	±2°	XX	±0.05	.XX	±1°	XXX	±0.03	.XXX	±0.5°	<p>深圳市精拓金电子有限公司</p>			
X	±0.15	.X	±5°																				
X	±0.10	.X	±2°																				
XX	±0.05	.XX	±1°																				
XXX	±0.03	.XXX	±0.5°																				
单位 UNITS	MM	制图 DRAWING	许榕强	制图料号 PRODUCT PART NO.	905-751A2022D10201																		
比例 SCALE	1:1	审核 CHKD	郭治富	产品名称 PRODUCT NO.	AF/14.0沉板3.9刺破式四脚 前贴后鱼叉有边铁壳LCP黑色DIP																		
日期 DATE	2016-09-09	核准 APPD	黄国荣	角法 VIEW	版本 VER																		
				版本 VER	A0																		