

SAMZO REAC/ROHS

REV	ECN NO	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2018.06.14






Performance Specifications

1. Rated Current: 5.0A
2. Rated Voltage: 12V
3. Withstand Voltage: 500V
4. Contact Resistance: $\leq 30m\Omega$
5. Insulation Resistance: 500M Ω
6. Operating Temperature: -40° C to +85° C

26 E 4 1 * 0 2 0
 (A) (B) (C) (D) (E) (F) (G) (H)

- A. Series: 26: 2.0 - 53 series
- B. Spring contact pitch: E - 2.0mm
- C. Fixing method: 4 - Horizontal Mounting
- D. Product height: 1 - H2.0mm
- E. PIN NO: 2-2P/3-3P/4-2P/5-5P/6-6PIN
- F: Main body material: 0 - LCP
- G: Spring contact material: 2 - Brass
- H: Mold code: 0 - convention

26E41-6-020	13.90	10.00	8.00
26E41-5-020	11.90	8.00	6.00
26E41-4-020	9.90	6.00	4.00
26E41-3-020	7.90	4.00	2.00
26E41-2-020	5.90	2.00	4.00
BE FILLED	DIM A	DIM B	DIM C



RECOMMENDED PCB LAYOUT
 TOL: (±0.05)

ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR					
B	塑胶	LCP	1	黑色	CHECKED	ZHENGUILAN	2018.06.12	$\geq 0 \sim 2 <$	± 0.15
A	触点	黄铜	1	镀金	APPROVED	LILIANJIANG	2018.06.14	$\geq 2 \sim 5 <$	± 0.25
								$\geq 0 \sim 2 <$	± 0.15
								≥ 5	± 0.35

FIRST VIEW

SCALE 1:1 UNIT mm

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM

SAMZO COMPONENTS
 Electronic switch and connector manufacturer

TITLE:	卧贴刀片电池公座H2.00MM
DWG NO:	26E41-P001
PART NO:	26E4120D006
MODEL NO:	26E41-* -020
NAME:	DC CONN