




客户图



RECOMMENDED PCB LAYOUT

Note:

1: Material (材料):

- Housing: PA9T (胶芯: PA9T)
- Barrel: Brass C3604 (针管: 黄铜 C3604)
- Plunger: Brass C3604 (针管: 黄铜 C3604)
- Spring: SUS304 (弹簧: SUS304)
- Magnet: NdFeB (磁铁: 钕铁硼)

2: Plating (电镀):

- Barrel: 3u' Au over 50u'~80u' Ni (针管: 镀金3u', 镍底50u'~80u'.)
- Plunger: 3u' Au over 50u'~80u' Ni (针头: 镀金3u', 镍底50u'~80u'.)
- Magnet: Ni plated (镀镍)
- Spring: Not plated (弹簧: 不电镀)

3: Electrical (电气特性):

- Rated Current & Voltage: DC 12V, 1A (额定电压&电流: 直流12V, 1A)
- Contact Resistance: 50 mohm Max. at working height. (接触电阻: 最大50毫欧 (在工作高度状态下))
- Insulation Resistance: 1,000MΩ minimum. (绝缘电阻: 1,000MΩ以上)
- Dielectric Withstand Voltage: 500VAC/minute. (抗击电压: 500VAC/minute)

4: Mechanical (机械性能):

- Force: 30g±8g at working height. (30g±8g 在工作高度)
- Durability: 10,000 cycles (min) (寿命: 10000次)

5: Work Temperature (工作环境):

- Withstanding Higt Temperature: 280℃
- Operational Temperature: -20℃~ +70℃

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL: 0755-28773277 FAX: 0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2022.3.24	VER.	A.1

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.5°
X.X	±0.10mm	X.X	±1.0°
X.	±0.20mm	X.	±2.0°

DESIGNED BY:		DWG. NO.	YZ00415040R-04025-01
CHECKED BY:		TITLE:	Pogo pin 连接器
APPROVED BY:			