



PARTS DIMENSION TABLE


parts no.	DIM. a	DIM. b	inner thread
1	4.8	11.8	4#40
2	5.8	12.8	4#40

说明:

1. 特性:  
 额定电压 :500V AC MAX.  
 小针额定电流 :5A  
 大针额定电流 :10A, 20A, 30A, 40A  
 接触阻抗 :30mΩ MAX.  
 绝缘阻抗 :3000MΩ MIN. at 500V DC  
 耐电压值 :1000V AC RMS for 1Minute  
 温度范围 : -55℃~+105℃  
 盐雾时间 : 48H
2. 材料:  
 胶芯 : PBT, rated UL94V-0  
 接触点: 铜合金, 镀金1u"-30u"  
 铁壳 : SPCC, 前壳镀镍后壳镀锡  
 支架 : SPCC, 镀镍  
 鱼叉 : 铜合金, 镀锡  
 铆钉 : 铜合金, 镀镍  
 螺丝 : 铁合金, 镀镍



额定电源	∅A	PCB孔∅B
10A	∅1.80	∅2.00
20A	∅2.80	∅3.00
30A	∅3.30	∅3.50
40A	∅3.80	∅4.00



Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: DWR-8W8M 公头 弯插 全金 锁Z字片 四方鱼叉			
DRAWN: LYF	DATE: 2024-06-02	PART. NO.	D-DWR08WPM-E000		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DWR-00044	REV.	A QTOO