








Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE $\pm$ 0.05)

TOLERANCE TABLE	
.0	$\pm$ 0.30
.00	$\pm$ 0.20
.000	$\pm$ 0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: DWR-25W3M 公头 弯插 全金 锁Z字片 四方鱼叉			
DRAWN: LYF	DATE: 2024-06-02	PART. NO.	D-DWR025PM-E000		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DWR-00052	REV.	A QT00

说明:

1. 特性:

额定电压 :500V AC MAX.

小针额定电流 :5A

大针额定电流 :10A, 20A, 30A, 40A

接触阻抗 :30m Ω MAX.

绝缘阻抗 :3000M Ω MIN. at 500V DC

耐电压值 :1000V AC RMS for 1Minute

温度范围 : -55 $^{\circ}$ C +105 $^{\circ}$ C

盐雾时间 : 48H

2. 材料:

胶芯 : PBT, rated UL94V-0

接触点: 铜合金, 镀金1u"-30u"

铁壳 : SPCC, 前壳镀镍后壳镀锡

支架 : SPCC, 镀镍

鱼叉 : 铜合金, 镀锡

铆钉 : 铜合金, 镀镍

螺丝 : 铁合金, 镀镍

额定电源	$\varnothing$ A	PCB孔 $\varnothing$ B
10A	$\varnothing$ 1.80	$\varnothing$ 2.00
20A	$\varnothing$ 2.80	$\varnothing$ 3.00
30A	$\varnothing$ 3.30	$\varnothing$ 3.50
40A	$\varnothing$ 3.80	$\varnothing$ 4.00