

说明:

1. 特性:

额定电压 :500V AC MAX.

小针额定电流 :5A

大针额定电流 :10A, 20A, 30A, 40A

接触阻抗 :30mΩ MAX.

绝缘阻抗 :3000MΩ MIN. at 500V DC

耐电压值 :1000V AC RMS for 1Minute

温度范围 : -55℃~+105℃

盐雾时间 : 48H

2. 材料:

胶芯 : PBT, rated UL94V-0

接触点: 铜合金, 镀金1u"-30u"




铁壳 : SPCC, 前壳镀镍后壳镀锡

支架 : SPCC, 镀镍

鱼叉 : 铜合金, 镀锡

铆钉 : 铜合金, 镀锡

螺丝 : 铁合金, 镀锡



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

| 额定电源 | ØA | PCB孔ØB |
|------|-------|--------|
| 10A | Ø1.80 | Ø2.00 |
| 20A | Ø2.80 | Ø3.00 |
| 30A | Ø3.30 | Ø3.50 |
| 40A | Ø3.80 | Ø4.00 |

TOLERANCE TABLE

| | |
|------|-------|
| .0 | ±0.30 |
| .00 | ±0.20 |
| .000 | ±0.05 |

| | | | | | |
|---------------|---------------------|--|-----------------|-------|------|
| APPROVED: | DATE: | Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD | | | |
| CHECKED: | DATE: | TITLE: DWR-13W6F 母头 弯插 全金 锁Z字片 四方鱼叉 | | | |
| DRAWN: LYF | DATE: 2024-06-02 | PART. NO. | D-DWR13WPF-E000 | | |
| | | UNIT | mm | SCALE | free |
| | | FILE NO. | Ckmtw-DWR-00047 | REV. | A |