




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2025.06.19	
A2	ECN-P-2025120401			2025.12.04	



■SPECIFICATIONS

- Voltage rating:250V AC/DC
- Current rating:7A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤20mΩ

PART NO.:

X5050 H M-04-N2

Series No
Category:H-HSG
Welding Board Angle:
M-Male housing
Row No.Pin No:XX-02P
Material:N2-PA66 UL94V-0

X5050HM-04-N2	Nylon 66 UL 94V-2	X5050TF	X5050W X5050HF
PART NO	Material	Suitable XKB Terminal	Mates With XKB Wafer Or Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: 5.08mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X5050HM-04-N2
APPROVED		SIZE: A4	DWG NO.: