

Distribution Box



Metal Distribution Box

Features

- Continuously welded seams Foam-in-place seamless gasket 120-degree opening heavy-duty industrial hinges
- IP66 protection rating against dust and water according to IEC 60529 & anti-collision according to IEC 62262 IK10
- RAL 7035 outdoor powder coating; gland plate on bottom
- Right hand opening; door interchangeable
- Custom cutouts available

Part No.	Dimensions (WxLxD)	Anti-collision Level	IP Level	Gland Plate	Lock Q'ty
FT 202015	200x200x150mm	IK10	66	ax1	1
FT 302015	200x300x150mm	IK10	66	ax1	1
FT 302515	250x300x150mm	IK10	66	ax1	1
FT 302520	250x300x200mm	IK10	66	ax1	1
FT 303015	300x300x150mm	IK10	66	bx1	1
FT 303020	300x300x200mm	IK10	66	bx1	1
FT 304015	400x300x150mm	IK10	66	ax2	1
FT 304020	400x300x200mm	IK10	66	cx1	1
FT 403015	300x400x150mm	IK10	66	bx1	1
FT 403020	300x400x200mm	IK10	66	bx1	1
FT 404020	400x400x200mm	IK10	66	ax1	1
FT 404030	400x400x300mm	IK10	66	ax1	1
FT 406020	600x400x200mm	IK10	66	bx1	1
FT 406030	600x400x300mm	IK10	66	bx1	1
FT 503020	300x500x200mm	IK10	66	ax2	2
FT 504020	400x500x200mm	IK10	66	cx1	2
FT 504025	400x500x250mm	IK10	66	cx1	2
FT 505020	500x500x200mm	IK10	66	cx1	2
FT 505025	500x500x250mm	IK10	66	cx1	2

Part No.	Dimensions (WxLxD)	Anti-collision Level	IP Level	Gland Plate	Lock Q'ty
FT 604020	400x600x200mm	IK10	66	cx1	2
FT 604030	400x600x300mm	IK10	66	cx1	2
FT 605025	500x600x250mm	IK10	66	cx1	2
FT 606020	600x600x200mm	IK10	66	dx1	2
FT 606025	600x600x250mm	IK10	66	dx1	2
FT 606030	600x600x300mm	IK10	66	dx1	2
FT 606040	600x600x400mm	IK10	66	dx1	2
FT 705020	500x700x200mm	IK10	66	cx1	2
FT 705025	500x700x250mm	IK10	66	cx1	2
FT 806020	600x800x200mm	IK10	66	dx1	2
FT 806030	600x800x300mm	IK10	66	dx1	2
FT 806040	600x800x400mm	IK10	66	dx1	2
FT 808025	800x800x250mm	IK10	66	cx2	2
FT 808030	800x800x300mm	IK10	66	cx2	2
FT 1006025	600x1000x250mm	IK10	66	dx1	3
FT 1006030	600x1000x300mm	IK10	66	dx1	3
FT 1006040	600x1000x400mm	IK10	66	dx1	3
FT 1008025	800x1000x250mm	IK10	66	cx2	3
FT 1008030	800x1000x300mm	IK10	66	cx2	3
FT 1206030	600x1200x300mm	IK10	66	dx1	3
FT 1206040	600x1200x400mm	IK10	66	dx1	2

Part No.	Dimensions (WxLxD)	Anti-collision Level	IP Level	Gland Plate	Lock Q'ty
ST202015	200x200x150mm	IK10	66	ax1	1
ST203015	200x300x150mm	IK10	66	ax1	1
ST253015	250x300x150mm	IK10	66	ax1	1
ST253020	250x300x200mm	IK10	66	ax1	1
ST303015	300x300x150mm	IK10	66	bx1	1
ST303020	300x300x200mm	IK10	66	bx1	1
ST304015	300x400x150mm	IK10	66	bx1	1
ST304020	300x400x200mm	IK10	66	bx1	1
ST305015	300x500x150mm	IK10	66	bx1	1
ST305020	300x500x200mm	IK10	66	bx1	1
ST403015	400x300x150mm	IK10	66	bx1	1
ST403020	400x300x200mm	IK10	66	cx1	1
ST404020	400x400x200mm	IK10	66	cx1	1
ST405015	400x500x150mm	IK10	66	bx1	1
ST405020	400x500x200mm	IK10	66	cx1	1
ST405025	400x500x250mm	IK10	66	cx1	1
ST406020	400x600x200mm	IK10	66	cx1	2
ST406025	400x600x250mm	IK10	66	cx1	2
ST406030	400x600x300mm	IK10	66	cx1	2
ST505020	500x500x200mm	IK10	66	dx1	1
ST505025	500x500x250mm	IK10	66	dx1	1
ST506020	500x600x200mm	IK10	66	dx1	2
ST506025	500x600x250mm	IK10	66	dx1	2
ST507020	500x700x200mm	IK10	66	dx1	2
ST507025	500x700x250mm	IK10	66	dx1	2

Part No.	Dimensions (WxLxD)	Anti-collision Level	IP Level	Gland Plate	Lock Q'ty
ST604020	600x400x200mm	IK10	66	dx1	1
ST604025	600x400x250mm	IK10	66	dx1	1
ST604030	600x400x300mm	IK10	66	dx1	1
ST606020	600x600x200mm	IK10	66	dx1	2
ST606025	600x600x200mm	IK10	66	dx1	2
ST606030	600x600x300mm	IK10	66	dx1	2
ST606040	600x600x400mm	IK10	66	dx1	2
ST608020	600x800x200mm	IK10	66	dx1	2
ST608025	600x800x250mm	IK10	66	dx1	2
ST608030	600x800x300mm	IK10	66	dx1	2
ST6010020	600x1000x200mm	IK10	66	dx1	3
ST6010025	600x1000x250mm	IK10	66	dx1	3
ST6010030	600x1000x300mm	IK10	66	dx1	3
ST6010040	600x1000x400mm	IK10	66	dx1	3
ST6012020	600x1200x200mm	IK10	66	dx1	3
ST6012030	600x1200x300mm	IK10	66	dx1	3
ST6012040	600x1200x400mm	IK10	66	dx1	3
ST705020	700x500x200mm	IK10	66	dx1	1
ST705025	700x500x250mm	IK10	66	dx1	1
ST808025	800x800x250mm	IK10	66	cx2	2
ST808030	800x800x300mm	IK10	66	cx2	2
ST8010025	800x1000x250mm	IK10	66	cx2	3
ST8010030	800x1000x300mm	IK10	66	cx2	3
ST8012030	800x1200x300mm	IK10	66	cx2	3