

	1	2	3	4	5	6	7	8																																						
	linear dimension(Tolerances Standard GB/T 14486-2008)							—	$\square$	$\perp$																																				
A	variable range	to 6	over 6 to 10	over 10 to 30	over 30 to 60	over 60 to 100	over 100 to 160	to 10	to 10	to 100		版本 Version	描述 Description	设计 Design	批准 Approved	日期 Date																														
	tolerance	$\pm 0.20$	$\pm 0.30$	$\pm 0.50$	$\pm 0.70$	$\pm 1.00$	$\pm 1.30$	$\pm 1.60$	0.10	0.30	0.60	A	新发行	熊武敌	楼特高	2024.03.10																														
B											<b>材质及电镀 MATERIAL</b>																																			
C											螺丝 Screws		M3.0, 钢, 镀锌 M3.0, Steel, Zn plated		方块 Cage		铜合金, 镀镍 Copper alloy, Ni plated		焊脚 Pin header		铜合金, 镀锡 Copper alloy, Tin plated		塑件 Housing		PA66, UL94V-0																					
D											<b>电气性能 ELECTRICAL</b>				参考标准 Stanard		UL IEC		额定电压 Rated voltage		300V 400V		额定电流 Rated current		20A 24A																					
E											使用线径 Wire range		24-12AWG 2.5mm <sup>2</sup>		接触电阻 Contact resistance		20m $\Omega$		绝缘电阻 Insulation resistance		500M $\Omega$ /DC500V		耐电压 Withstanding voltage		AC1600V/1Min																					
F											<b>机械性能 MECHANICAL</b>				温度范围 Temp. range		-40 $^{\circ}$ C ~ +105 $^{\circ}$ C		瞬时温度 Max. soldering		+250 $^{\circ}$ C for 5 Sec		扭矩 Torque		5.10kgf.cm/0.5N.m																					
G											剥线长度 Strip length		6~7mm		编码原则(Product Number Code): WJ129V-5.0-XXP-1Y-00A 产品型号(Series No.)   间距(Pitch)   极数(No. of Poles)   客户需求(Customer Request)   塑体颜色(Housing Color)																															
H											1: 单倍间距 (Single Pitch)		2: 双倍间距 (Double Pitch)		1: 灰色(Grey)		2: 蓝色(Blue)		3: 黑色(Black)		4: 绿色(Green)		5: 橙色(Orange)		6: 红色(Red)		7: 透明(Transparent)		8: 黄色(Yellow)		9: 白色(White)															
											<b>第三视角 (THIRD ANGLE PROJECTION)</b>				<b>螺钉式PCB接线端子</b>				<b>PCB SCREW TERMINAL BLOCK</b>				<table border="1"> <tr> <td>图纸类型 (TYPE)</td> <td>CUSTOMER DRAWING</td> <td>型号 (NAME)</td> <td>WJ129V-5.0-XXP-1Y-00A</td> </tr> <tr> <td>单位 (UNITS)</td> <td>mm</td> <td>版本 (VERSION)</td> <td>A</td> </tr> <tr> <td>尺寸 (SIZE)</td> <td>A4</td> <td colspan="2">            宁波康奈克斯电气有限公司            Ningbo Kangnex Electric Co., Ltd         </td> </tr> <tr> <td>比例 (SCALE)</td> <td>1:1</td> <td colspan="2"></td> </tr> <tr> <td>图页 (SHEET)</td> <td>1/1</td> <td colspan="2"></td> </tr> </table>				图纸类型 (TYPE)	CUSTOMER DRAWING	型号 (NAME)	WJ129V-5.0-XXP-1Y-00A	单位 (UNITS)	mm	版本 (VERSION)	A	尺寸 (SIZE)	A4	宁波康奈克斯电气有限公司 Ningbo Kangnex Electric Co., Ltd		比例 (SCALE)	1:1			图页 (SHEET)	1/1		
图纸类型 (TYPE)											CUSTOMER DRAWING	型号 (NAME)	WJ129V-5.0-XXP-1Y-00A																																	
单位 (UNITS)											mm	版本 (VERSION)	A																																	
尺寸 (SIZE)	A4	宁波康奈克斯电气有限公司 Ningbo Kangnex Electric Co., Ltd																																												
比例 (SCALE)	1:1																																													
图页 (SHEET)	1/1																																													
	1	2	3	4	5	6	7	8																																						