





REV.	DESCRIPTION	ECN NO.	NAME	DATE

SPECIFICATIONS

Current Rating: 3Amps
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester (UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 240°C for 30-60 seconds
 (260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE: ±0.05 (TOP VIEW)



P/N	PIN	DIM.A	DIM.B
A254UP-ZD01P-PC3.0	1	0.00	2.54
A254UP-ZD02P-PC3.0	2	2.54	5.08
A254UP-ZD03P-PC3.0	3	5.08	7.62
A254UP-ZD04P-PC3.0	4	7.62	10.16
A254UP-ZD05P-PC3.0	5	10.16	12.70
A254UP-ZD06P-PC3.0	6	12.70	15.24
A254UP-ZD07P-PC3.0	7	15.24	17.78
A254UP-ZD08P-PC3.0	8	17.78	20.32
A254UP-ZD09P-PC3.0	9	20.32	22.86
.....
A254UP-ZD40P-PC3.0	40	(PIN-1)X2.54	(PIN)X2.54

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				
DIM.	TOL.	TITLE: 2.54PH H2.5 1xnPin 180度 PC3.0 PA6.0 PB2.5 L11.5 6T				
x.	±0.30	DWG. NO.: A254UP-ZDXP-PC3.0		CHECKED: MAX		
x.x	±0.20	PART NO.: A254UP-ZDXP-PC3.0		DRAWN: ELLA		
x.xx	±0.10	UNIT: mm		SCALE: none		
GENERAL ANGLE:		SHEET: 1 of 1		DWG. SIZE: A4		
x°	±5'	LAYER: bxconn		APPROVED: WILL		
x.x°	±1'					
x.xx°	±0.5'					