





“*” Pivot Dimension

RoHS Component

RoHS Component



PCB LAYOUT

NOTICE :



1. ELECTRIC:

- DIELECTRIC RATING: 300V
- CONTACT CURRENT RATING: 5AMP
- CONTACT RESISTANCE: 15mΩ MAX.
- INSULATION RESISTANCE: 1000MΩ MIN. at 500V DC
- DIELECTRIC STRENGTH: 500V AC RMS for 1Minute
- OPERATION TEMPERATURE: -55C° ~125C°

2. MATERIAL:

- INSULATOR: PBT+30% G.F (UL94V-0)
- CONTACT: COPPER ALLOY
- CONTACT PLATED: GOLD FIASH OVER NICKEL
- SHELL: SPCC
- SHELLPLATED: NICKEL/TIN
- FORK: COPPER ALLOY NICKEL/TIN

浙江创都电子科技有限公司

TOLERANCE: XX ±0.38 XXX ±0.25 XXXX ±0.13 X* ±5° XX* ±2°	DRAWN BY : _____	DATE : 2009. 11. 21	PART NAME: HDP 50P 公 直焊板式铆6.0鱼叉 锁4-40UNC*4.8螺丝QH	
	CHECKED BY: _____	DATE : 2009. 11. 25	DRAW NO. DP-G-50P-ZC-YCLS	PART NO. _____
 	APPROVED BY: _____	DATE : 2009.11.25	REMARK _____	MOLD NO. _____
UNIT: mm [inch] SCALE:1:1 SIZE: A4				