





REVISION			
LTR	DESCRIPTION	DATE	APP
AO	NEW RELEASE	07/15/2021	PECK



Note:

1.Material:

- 1.1 Housing: High temperature thermoplastic,UL94v-0
- 1.2 Orbit: High temperature thermoplastic,UL94v-0
- 1.3 Contact: copper alloy;;
Gold plated contact area;Tin plated solder area
- 1.4 Shell:Stainless;Ni plated allover;
Gold plated solder area

2.Specification:

- 2.1 Current rating: 0.1A Max
- 2.2 Voltage rating: 30 V DC
- 2.3 Dielectric withstanding voltage:
500V(AC) for 1 min.
- 2.4 Contact resistance: 100mΩ Max.
- 2.5 Insulation resistance: 1000MΩ min.
- 2.6 Temperature range: -15°C~65°C
- 2.7 Mating cycle:50000cycles min
- 2.8 Insert force: 0.5N Max



DIMENSION CLASSIFICATION		台灣碩方精密電子科技有限公司 TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD				開關, 連接器 SOFNG	
■	CRITICAL	TITLE		TC-628			
☒	MAJOR	TOLERANCE TABLE		PART NO.		SOF-G006	
.X	± 0.40	APPROVED		Peck		DWG NO.	
.XX	± 0.25	CHECKED		Paul		SCALE 1:1	
.XXX	± 0.10	DRAWIN		David		REV	
ANGLE	± 2°					SHEET NO.	
						SD106	
						A4	
						1/1	