




"*" Pivot Dimension

RoHS Component



NOTICE :

- 1. ELECTRIC:
 - DIELECTRIC RATING: 300V
 - CONTACT CURRENT RATING: 3AMP
 - CONTACT RESISTANCE: 15mΩ MAX.
 - INSULATION RESISTANCE: 1000MΩ MIN. AT 500V DC
 - DIELECTRIC STRENGTH: 500V AC RMS FOR 1MINUTE
 - OPERATION TEMPERATURE: -55°C ~ 125°C
- 2. MATERIAL:
 - INSULATOR: PBT+30% G.F(UL94V-0)
 - CONTACT: COPPER ALLOY
 - CONTACT PLATED: GOLD FLASH OVER NICKEL
 - SHELL: SPCC
 - SHELL PLATED: NICKEL/TIN

浙江创都电子科技有限公司

TOLERANCE: XX ±0.38 XXX ±0.25 XXXX ±0.13 X° ±5° XX° ±2°	DRAWN BY :	DATE :	PART NAME:	
			2009.11.21	HDB 78 母 焊线式传统铆合QW
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	CHECKED BY :	DATE :	DRAW NO.	HDD-M-78P-HX-GK
			2009.11.25	PART NO.
	APPROVED BY :	DATE :	REMARK	
		2009.11.25	MOLD NO.	